
EAO – Your Expert Partner for Human Machine Interfaces

704.405.0 - Selector switch actuator 3 positions, short lever

704.405.0 - Selector switch actuator 3 positions, short lever



Attention: The preview is based on a sample product. This can differ from your current configuration.

Mounting

Mounting cut-out Design

Front

Front dimension Front shape Front bezel colour Front bezel material

Other Attributes Weight

0,037 kg

Plastic

non-illuminative

black

short

IP65

Ø 22,3 mm

raised

Ø 29 mm

Aluminium

natural anodized

round

Operating-/Indication part

Lever material Lever colour Switching angle Lever illumination Lever shape

IP-Rating Front protection

From protection

Actuator Switching action

Switching element

Rotary positions3max. number of switching3elements

Function


Selector switch



EAO – Your Expert Partner for Human Machine Interfaces


704.405.0 - Selector switch actuator 3 positions, short lever

Dimensions



X = Screw terminal

Mounting cut-outs




PIT = Push-in terminal

Wiring diagram



Switching positions



Additional information

Max. 3 switching elements can be clipped on The colour of anodized aluminium parts can vary due to technical production reasons

Legend Switching action: A = Rest, B = Momentary

