

**MNX PC 150/50 LT**



Sample photo

**Order symbol:** PC 150/50 LT  
**Product nbr:** 6012914  
**Description:** Enclosure, PC  
**Remarks:** Smoked transparent cover

**EAN:** 6418074022387  
**EI. number:**  
 Finland: 3420453  
 Electric No. Denmark: 8212022438  
 Electric No. Italy: 7352075  
 Electric No. Sweden: 2535642

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
<b>mm:</b>	180	130	50	MIN 10	DIN-15 Mounting rail
<b>inch:</b>	7.1	5.1	2.0	MIN 15	DIN-15 Mounting rail
				MIV 10	DIN-35 Mounting rail
				MIV 15	DIN-35 Mounting rail
				FP A 150/180	Front plate (Aluminium)
				HFP 180	Front plate hinge series
				FP 22046	Wall fastening lug (4 pcs)
Materials:				Rating:	
<b>Material:</b>	Polycarbonate			Ingress Protection (EN 60529): IP66/IP67	
<b>Base colour:</b>	RAL 7035 -light grey			Impact Resistance (EN 62262): IK08	
<b>Cover screws material:</b>	Polyamide			Electrical insulation: Totally insulated	
<b>Cover colour:</b>	Smoked grey			Halogen free (DIN/VDE 0472, Part 815): 1	
<b>Cover screws colour:</b>	Black			UV resistance: UL 508	
<b>Gasket material:</b>	TPE			Flammability Rating: UL 746C 5"	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 1, 4, 4X, 6	
Temperatures:				Certificates:	
<b>Temperature °C (short term):</b>	-40 ... 120 °C			Germanischer Lloyd (GL)	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			SGS Fimko	
<b>Temperature °F (short term):</b>	-40 ... 250 °F			Gost R	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F				
Accessories:					
MIV 150	Mounting plate (Galvanized steel)				

