

CARDMASTER PC 36/31-3



Sample photo

Order symbol: PC 36/31-3
Product nbr: 7525020
Description: Enclosure, PC
Remarks: Smoked transparent hinged cover

EAN: 6418074056757
El. number:
 Finland: 3438234
 Electric No. 8212016680
 Denmark:
 Electric No. Sweden: 2537310

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	390	316	167	FP 36/31	Front plate (aluminium)
inch:	15.4	12.4	6.6		
Materials:				Rating:	
Material:	Polycarbonate			Ingress Protection (EN 60529): IP65	
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK07/IK08	
Cover colour:	Smoked grey			Electrical insulation: Totally insulated	
Gasket material:	EPDM & PUR			Halogen free (DIN/VDE 0472, Part 815): 1	
Temperatures:				UV resistance: UL 508	
Temperature °C (short term):	-40 ... 120 °C			Flammability Rating: UL 746C 5"	
Temperature °C (continuous):	-40 ... 80 °C			Glow Wire Test (IEC 695-2-1) °C: 960	
Temperature °F (short term):	-40 ... 250 °F			NEMA Class: NEMA 1, 3, 3R, 12, 13	
Temperature °F (continuous):	-40 ... 175 °F			Certificates:	
Accessories:				SGS Fimko	
MP 36/31	Mounting plate			Gost R	

