

1m Thunderbolt Cable - M/M

StarTech ID: TBOLTMM1M



Our 1m (3.28ft) Thunderbolt™ cables offer a high quality solution for harnessing the speed and power of Thunderbolt™ technology, delivering full 10Gbps performance while combining both data and video into a single high-performance cable.

The cables support daisy chaining of up to 6 compatible devices, which ensures streamlined performance and easier setup. Plus, with dual channel, bi-directional data transfer capability and support for power delivery (for bus-powered devices), these Thunderbolt cables offer the robust performance needed for optimal connections.

This high quality Thunderbolt™ cable is specifically designed to provide a clutter-free solution for device connections of up to 1m, providing enough cable length to connect compatible devices.

Backed by our 2-year Manufacturer's Warranty.

Applications

- Connecting a Thunderbolt™-equipped computer to a nearby Thunderbolt-enabled device, such as an external drive enclosure or RAID array
- Connecting two Thunderbolt-equipped Mac® computers, for Target Disk Mode file transfers
- Connect a Thunderbolt-equipped MacBook Pro® to an iMac®, to use the iMac as the display for the MacBook Pro

Features

- Dual-channel, simultaneous bi-directional data and video transfers up to 10 Gbps
- Supports Power-over-cable, for bus-powered Thunderbolt devices

Technical Specifications

Warranty	2 Years
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Connector Plating	Nickel
Connector A	1 - Thunderbolt™ (20-pin) Male
Connector B	1 - Thunderbolt™ (20-pin) Male
Cable Length	3.3 ft [1 m]
Color	Black
Product Length	3.3 ft [1 m]
Product Weight	1.8 oz [50 g]
Wire Gauge	34 AWG
Package Quantity	1
Shipping (Package) Weight	0.1 lb [0.1 kg]
Included in Package	1 - 1 m Thunderbolt Cable - M/M

Certifications, Reports and Compatibility

