

Circus

CIR025720

Old item no.: 17980WT



Circus T45 Wh 122 840 3,5D CLA NA

Circus is specially designed to withstand the rigors of everyday use in industrial and manufacturing environments as well as cosmetology, health spas, beauty salons and clean room applications where FOD is a concern. No knobs to tighten, nothing to adjust. A 3.5-diopter white crown optical-quality glass lens provides distortion-free viewing. The highly-flexible, self-balancing shade and 45" internal spring arm allows the lamp head to be positioned horizontally, vertically or laterally. Edge clamp mount. Color: white.



Lightsource

Number of lamps	1
Lamp power (W)	22
Lamp base	2GX13
Lightsource	Fluorescent circular T5-C
CRI and/or Color Temperature	80 CRI, 4000K

Optic

Primary Lens (D)	3.5
Working distance (mm)	285.7
Magnification (X)	1.88

Dimensions

Net weight (kg)	5,1
Arm length (in.)	39

Electrical data

Maximum frequency (Hz)	60
Minimum frequency (Hz)	50
Maximum voltage (V)	120
Voltage from (V)	100
Total consumption (W)	23

Technical data

Maximum ambient temperature (°C)	25
IP classification	20

Termination

Plug type	NA
Cord length (ft)	6

Body

Body color	Grey
------------	------

Circus
CIR025720



Circus T45 Wh 122 840 3,5D CLA NA

Circus is specially designed to withstand the rigors of everyday use in industrial and manufacturing environments as well as cosmetology, health spas, beauty salons and clean room applications where FOD is a



Photos




Circus
CIR025720



Circus T45 Wh 122 840 3,5D CLA NA

Circus is specially designed to withstand the rigors of everyday use in industrial and manufacturing environments as well as cosmetology, health spas, beauty salons and clean room applications where FOD is a concern. No knobs to tighten, nothing to adjust. A 3.5-diopter white crown optical-quality glass lens provides distortion-free viewing. The self-balancing shade and 45" internal spring arm allows



Drawings

