

IFM Magnifiers

16350LG

Old item no.: 16350LG



IFM2A 3D 3C LIGHT GRAY/GRIS

IFM is an ideal lighter-duty magnifier for low-power inspection. A 22W circline fluorescent lamp provides 360° shadow-free illumination and a lamp diffuser cover protects the bulb from damage. 3-diopter (1.75X) lens. 30" external spring-balanced arm. Edge clamp mount. Color: light grey.



Lightsource

Number of lamps	1
Lamp power (W)	22
Lamp base	G10Q
CRI and/or Color Temperature	4100K
Lightsource	T9

Optic

Color of reflector	White
Material of reflector	PC
Working distance (mm)	333
Magnification (X)	1.75

Body

Body material	Steel
Body color	Grey

Electrical data

Maximum frequency (Hz)	60
Minimum frequency (Hz)	50
Maximum voltage (V)	120
Voltage from (V)	100

Dimensions

Net weight (kg)	0
Gross weight (lb.)	9
Arm length (in.)	30

Termination

Cord length (ft)	6
Mounting	Edge clamp

Ballast

Type of Ballast	Electromagnetic
-----------------	-----------------