

LFM LED

LFL026106

Old item no.: 18345LG



LFM LED T100 Lg500 840 3DCLANA

LFM LED is Luxo's most cost-effective LED Magnifier. A die-cast aluminum housing and flexible, 45" spring-balanced L-arm ensure the magnifier can be placed in any position. Auto shut-off and dimming features ensure energy savings. LFM LED is suitable for a variety of Industrial applications. 3-diopter (1.75X) lens. Edge clamp mount. Color: light grey.



Lightsource

Number of lamps	1
Lamp power (W)	10
Lightsource	LED
CRI and/or Color Temperature	80 CRI, 4000K
Lumen/Watt	5.1
Lumen Out	50.5

Optic

Primary Lens (D)	3
Magnification (X)	1.75
Working distance (mm)	330

Dimensions

Net weight (kg)	2
Arm length (in.)	45

Electrical data

Maximum frequency (Hz)	60
Minimum frequency (Hz)	50
Maximum voltage (V)	120
Voltage from (V)	100
Total consumption (W)	10

Technical data

Maximum ambient temperature (°C)	25
IP classification	20

Body

Body color	Grey
------------	------

Termination

Mounting	Edge clamp
----------	------------

LFM LED
LFL026106



LFM LED T100 Lg500 840 3DCLANA

LFM LED is Luxo's most cost-effective LED Magnifier. A die-cast aluminum housing and flexible, 45" spring-balanced L-arm ensure the magnifier can be placed in any position. Auto shut-off and dimming features ensure energy savings. LFM LED is suitable for a variety of Industrial applications. 3-diopter (1.75X) lens. Edge clamp mount.



Drawings

