

KFM

KFK025789

Old item no.: 17253LG



KFM-2/FE 3D 3C Lg

KFM has a sturdy all-metal construction with a sleek design, flexible arm and excellent light output suitable for a variety of industrial, laboratory, cosmetology and low-vision applications. The flexibility of the neck assembly and patented internal spring 30" K-arm makes exact positioning easy. 3-diopter (1.75X) lens. Weighted base. Color: Light grey.



Optic

Color of reflector	White
Material of diffuser	Polycarbonate
Material of reflector	P C
Primary Lens (D)	3
Working distance (mm)	333
Magnification (X)	1.75

Electrical data

Maximum frequency (Hz)	60
Minimum frequency (Hz)	50
Maximum voltage (V)	120
Voltage from (V)	100

Body

Body color	Grey
Body material	Aluminum

Technical data

IP classification	20
-------------------	----

Lightsource

Number of lamps	1
Lamp power (W)	22
Lamp base	G10Q
CRI and/or Color Temperature	4100K
Lightsource	T9

Dimensions

Net weight (kg)	0
Arm length (in.)	30
Gross weight (lb.)	50

Termination

Mounting	Table/desk base
Cord length (ft)	6

Ballast

Type of Ballast	High frequency
-----------------	----------------