

IFM Magnifiers
16346WT

Old item no.: 16346WT



IFM1A 5D 3C WHITE/BLANC

IFM is an ideal lighter-duty magnifier for low-power inspection. A 22W circline fluorescent lamp provides 360° shadow-free illumination and a lamp diffuser cover protects the bulb from damage. 5-diopter (2.25X) lens. 45" external spring-balanced arm. Edge clamp mount. Color: white.



Lightsource

| | |
|------------------------------|-------|
| Number of lamps | 1 |
| Lamp power (W) | 22 |
| Lamp base | G10Q |
| CRI and/or Color Temperature | 4100K |
| Lightsource | T9 |

Optic

| | |
|-----------------------|-------|
| Color of reflector | White |
| Working distance (mm) | 200 |
| Material of reflector | PC |
| Magnification (X) | 2.25 |

Body

| | |
|---------------|-------|
| Body color | White |
| Body material | Steel |

Electrical data

| | |
|------------------------|-----|
| Maximum frequency (Hz) | 60 |
| Minimum frequency (Hz) | 50 |
| Maximum voltage (V) | 120 |
| Voltage from (V) | 100 |

Dimensions

| | |
|--------------------|----|
| Net weight (kg) | 0 |
| Gross weight (lb.) | 9 |
| Arm length (in.) | 45 |

Termination

| | |
|------------------|------------|
| Cord length (ft) | 6 |
| Mounting | Edge clamp |

Ballast

| | |
|-----------------|-----------------|
| Type of Ballast | Electromagnetic |
|-----------------|-----------------|