

# 87 26 250 T

## KNIPEX Cobra® VDE Hightech Water Pump Pliers, insulated with tether attachment point



- Adjustment by shifting one jaw directly on to the workpiece: fast, reliable and comfortable handling
- Fine adjustment: allows optimum adjustment to differently sized workpieces and comfortable handle position
- Good access to the workpiece
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- High load capacity having a slim design
- Guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened
- Pliers with integrated, insulated tether attachment point for a tool tether

<b>Article No.</b>	87 26 250 T
<b>EAN</b>	4003773081517
<b>Pliers</b>	chrome plated
<b>Handles</b>	
<b>Head</b>	
<b>Insulation standard</b>	IEC 60900 DIN EN 60900
<b>Adjustment positions</b>	24
<b>Capacity for pipes, inches (diameter) Ø Inch</b>	2
<b>Capacities for nuts mm</b>	46
<b>Capacities for pipes (diameter) Ø mm</b>	50
<b>Length mm</b>	250
<b>Net weight g</b>	397

technical change and errors excepted