

# 00 21 20

## Tool Case "Electric" 20 parts



- Heavy duty ABS material, black
- With circumferential double aluminium frame
- Register hinges working as lid holder
- Strong, ergonomic handle
- Two flip-locks, lockable
- One removable tool board in the lid with 15 push-in compartments on the bottom side and six big push-in compartments and a clamp compartment (400 mm width) on the lid side, fixed by push-button
- Base tray, height 58 mm, can be subdivided by flexible inserts; cover plate with six large push-in compartments, can be fixed by press button
- Cover and tool plate made of Con-Pearl® material
- 20 kg maximum load
- Dimensions, exterior (W x H x D): 480 x 180 x 365 mm dimensions, interior (W x H x D): 415 x 160 x 300 mm
- With 20 brand name tools, partly VDE tested according to DIN EN/IEC 60900

<b>Article No.</b>	00 21 20
<b>EAN</b>	4003773052166
<b>Net weight g</b>	7225


















technical change and errors excepted

Con-Pearl ist ein eingetragenes Warenzeichen der PARAT-WERK Schnbach GmbH & Co. KG



### Content 00 21 20 (20)

Article No.			Quantity	Nominal size	
03 06 180	Knipex	Combination Pliers	1	180 mm	
12 40 200	Knipex	Self-Adjusting Insulation Stripper	1	200 mm	
16 95 01 SB	Knipex	KNIPEX ErgoStrip®, Universal Dismantling Tool	1		
26 16 200	Knipex	Snipe Nose Side Cutting Pliers, (Stork Beak Pliers)	1	200 mm	
26 26 200	Knipex	Snipe Nose Side Cutting Pliers, (Stork Beak Pliers)	1	200 mm	
70 06 160	Knipex	Diagonal Cutter	1	160 mm	
74 06 160	Knipex	High Leverage Diagonal Cutter	1		
86 03 180	Knipex	Pliers Wrench, pliers and a wrench in a single tool	1	180 mm	
87 03 250	Knipex	KNIPEX Cobra®, Hightech Water Pump Pliers	1	250 mm	
95 16 200	Knipex	Cable Shears, with twin cutting edge	1	200 mm	
98 20 25	Knipex	Screwdrivers for slotted screws	1		
98 20 65 SL	Knipex	Screwdriver (Slim) for slotted screws	1		
98 20 55 SL	Knipex	Screwdriver (Slim) for slotted screws	1		

98 20 40 SL	Knipex	Screwdriver (Slim) for slotted screws	1		 1000 V  
98 24 01 SL	Knipex	Screwdriver (Slim) for cross-recessed screws, Phillips®	1		 1000 V  
98 24 02 SL	Knipex	Screwdriver (Slim) for cross-recessed screws, Phillips®	1		 1000 V  
98 25 01 SL	Knipex	Screwdriver (Slim) for cross-recessed screws, Pozidriv®	1		 1000 V  
98 25 02 SL	Knipex	Screwdriver (Slim) for cross-recessed screws, Pozidriv®	1		 1000 V  
98 52	Knipex	Cable Knife	1	185 mm	 1000 V 
005655	Wera	Voltage detector, single-pole, 247	1	0,5 x 3,0 x 70 mm	