



Proinstall-200-CH



Product Overview

Combined installation meter

Features

- loop resistance measurement
- Power internal resistance measurement
- short-circuit current measurement
- Niederohm- and continuity measurement
- insulation measurement
- RCD / FI measurement (contact voltage, trip time, trip current - increasing current)
- voltage and frequency measurement
- Testing of pole sensitive RCD / FI (type B)
- earth measurement (optional with probes)
- RCD / FI analysis to check all parameters of an RCD / FI

Device information

- Memory for approx. 1000 measurements with 3 levels for assigning distribution and circuit numbers
- IR / USB interface for transfer of the stored measured values to the PC
- Software for logging optionally available for the printout of a test report
- Integrated socket test with touch electrode to determine incorrectly connected Sockets or missing protective conductor
- Easy-to-read, large LC display with background lighting and a particularly large viewing angle
- Auto power off

Product highlights

- Compact and rugged design allows you to work even under difficult conditions (weighs only 1500g)
- Easy to use, intuitive user interface allows you immediately and to work efficiently
- Test probe with test button supplied available
- loop resistance measurement and short circuit current measurement without tripping the RCD / FI