



Datenblatt - Fiche technique - Data sheet


11.04.5810



ROLINE DisplayPort Kabel, 4K, DP ST - ST, 1,0 m

ROLINE Câble DisplayPort DP M - DP M, 1,0 m

ROLINE DisplayPort Cable, DP-DP, M/M, 1.0 m



Electrical Test :

- 100% Test(Open, Short, Miss Wire)
- Contact Resistance: 2 ohm Max
- Insulation Resistance: 10M ohm Min
- Hi-Pot: 100V DC/10ms


Table:

P/N	Length
11.04.5810	1000±30mm
11.04.5811	2000±50mm

DESCRIPTION :

- DisplayPort UL20276 [(30AWG*1PR+D+AL/MY)*5+30AW*4C]+AL/MY+BD
OD:6.0MM, Jacket Color: Black
- DisplayPort, Male, Pin: Gold Plated, Insulator: Black, Shell: Gold Plated
- DisplayPort, Shell: ABS, Color: Black
- DisplayPort, Shell: ABS, Color: Black
- Outer Molding: PVC 45P, Color: Black
- Inner Molding: PE

Pin Assignment



REV.	DATE	CONTENTS OF CHANGE	DESIGNER	TOL ±								APPROVAL	CHECK	DRAWING	DESIGN	DRAWING NAME	ROLINE DisplayPort Cable v1.3, DP-DP, M/M, Black	
				RANGE	Pla	Met	Ins	Por	Cab	Pac	Gas						DIS	DATE
①				0~6	0.1	0.1	0.1	0.2	0.5	1	0.5	0.2	PHILIP	PHILIP	henry	2016-12-05	11.04.5810 / 11.04.5811	
②				6~30	0.1	0.1	.15	.25	1	1	0.5	.25						
③				30~80	0.1	.15	0.2	0.3	2	1.5	1	0.3						
④				80~180	.15	.15	.25	0.3	2	2	1	.45						
⑤				180~315	.15	0.2	0.3	0.4	2.5	2	1	0.6						
⑥				315~800	0.2	0.3	0.4	0.5	3	3	2	1.1	SCALE	1:1	UNIT	MM		

