


**KEMET Part Number: PHE450MD6470JR30**  
(F450DW474J630ALW0L)

PHE450/F450, Film, Double Metallized Polypropylene, Commercial Grade, 0.47 uF, 5%, 630 V, 85C, Lead Spacing = 22.5mm



**Dimensions**

L	26mm MAX
H	23mm MAX
T	13.5mm MAX
S	22.5mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm
G	0.5mm NOM

**Packaging Specifications**

<b>Packaging:</b>	Bulk, Bag
-------------------	-----------

**General Information**

<b>Supplier:</b>	KEMET
<b>Series:</b>	PHE450/F450
<b>Dielectric:</b>	Double Metallized Polypropylene
<b>Style:</b>	Radial
<b>Features:</b>	Pulse
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>Miscellaneous:</b>	The Rated Voltage Decreases 1.3%/C Between +85C And +105C. Rthha= 40 C/W (85C), 0.2 m/s

**Specifications**

<b>Capacitance:</b>	0.47 uF
<b>Capacitance Tolerance:</b>	5%
<b>Voltage DC:</b>	630 VDC (85C), 466.2 VDC (105C)
<b>Voltage AC:</b>	400 VAC
<b>Temperature Range:</b>	-55/+105C
<b>Rated Temperature:</b>	85C
<b>Dissipation Factor:</b>	0.03% 1kHz, 0.06% 10kHz
<b>Insulation Resistance:</b>	14.1 GOhms
<b>Max dVdt:</b>	1,800 V
<b>Inductance:</b>	6 nH