

# Reciprocating Saw Blades

## Metal Cutting Blades



Mfrs. No.	Application
S 922 AF	Thin sheet metal 0.7-3mm, pipe and profile 5-100mm
S 922 EF	Thin sheet metal 1.5-4mm, pipe and profile 5-100mm
S 1122 HF	Thick sheet metal 3-8mm, pipe and profile 10-100mm
S 1122 BF	Thick sheet metal 3-8mm, pipe and profile 10-175mm
S 922 BF	Thick sheet metal 3-8mm, pipe and profile 10-100mm

Order Code
1358739
1358740
1358742
1358737
1358738

479394

5 blades per pack		
Size	Teeth Per Inch	Order Code
(mm)		
150 x 19 x 0.9	24	135-8739
150 x 19 x 0.9	18	135-8740
150 x 19 x 0.9	14	135-8742
225 x 19 x 0.9	14	135-8737
150 x 19 x 0.9	14	135-8738