



MICRO SWITCH

FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ - 2RM22 - A2

AKD1000

BZ-2RM22-A2
PAGE 1 OF 1

M

DRAWING NUMBER

9

ISSUE

REPLACES

RELEASE NO.

CHECK

18 JAN 06

RJ

CHECK

15 OCT 63

CHECK


15 OCT 63

CHECK

30 SEP 63

CHECK

30 SEP 63



REVISIONS

A	CO17410	6 CH	30 SEP 63
B	CO23414	6 CH	13 NOV 67
C	44382	6 CH	7 AUG 71
D	73287-J	6 CH	22 NOV 93
E	75204-B	6 CH	1 FEB 94
F	77588	6 CH	29 MAR 94
G	CO93346	6 CH	10 SEP 98
H	0018004	6 CH	18 JAN 06

FORMTEK
FO-80378

DRAWN
G C H

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE-----19 OZ MAX

RELEASE FORCE-----6 OZ MIN

PRETRAVEL-----.078 MAX

DIFFERENTIAL TRAVEL-----.001 - .011

OVERTRAVEL-----.078 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

-L96- 15 A - 125, 250, OR 480 VAC
1/2 A - 125 VDC; 1/4 A - 250 VDC
1/8 HP - 125 VAC; 1/4 HP - 250 VAC

-L288-
-L306-
-L315-

CE 05

16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE NOTED
DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT .077 LB