



**TNC PLUG - Straight & Right Angle**

Style	Times Cable	Belden Cable	a	b	c	d	CAI	Amphenol Part Number	Fig
Straight Plug	LMR200	RG 58	1.17(29.8)	.571(14.5)	.210	—	C36	<a href="#">31-2367-RFX</a>	1
Straight Plug	LMR240	9258	.984(25.0)	.571(14.5)	.220(5.6)	—	C36	<a href="#">31-6000-RFX</a>	2
Straight Plug	LMR400	9913,9914	1.67(42.4)	.571(14.5)	.49(12.4)	—	C36	<a href="#">31-6001-RFX</a>	3
Right Angle	LMR200	RG 58	—	—	—	—	C36	<a href="#">31-5849-RFX</a>	4
Right Angle	LMR240	9258	1.10	.57	.220	.86	C36	<a href="#">31-6003-RFX</a>	5
Right Angle	LMR400	9913, 9914	1.10	.57	.37	.86	C36	<a href="#">31-6002-RFX</a>	6