




Quality Products. Service Excellence.

## Rack Rail Reducer Panel *PBAS Series*



### Features

- Constructed in 14-gauge steel.
- EIA-310-D compliant round punched hole or tapped 10-32 for 19" mounting.
- Converts standard 23 or 24 inch rack mounting rails to 19 inch rack mounting.
- Sold in pairs.
- Finished in smooth black powder paint.
- RoHS Compliant.
- Manufactured in North America.

### Accessories

- Mounting Hardware

### 23 to 19 Inch Rack Rail Reducer Panel

Part No. 10-32 Tapped Black Finish	Mounting Dimensions	
	Rack Units	Height
PA2319001BK1	1U	1.75
PA2319003BK1	2U	3.50
PA2319005BK1	3U	5.25

### 24 to 19 Inch Rack Rail Reducer Panel

Part No. Clip-Nut Style Black Finish	Part No. Clip-Nut Style Light Gray Finish	Mounting Dimensions	
		Rack Units	Height
PBAS19001BK2	PBAS19001LG2	1U	1.75
PBAS19003BK2	PBAS19003LG2	2U	3.50
PBAS19005BK2	PBAS19005LG2	3U	5.25
PBAS19007BK2	PBAS19007LG2	4U	7.00
PBAS19008BK2	PBAS19008LG2	5U	8.75
PBAS19010BK2	PBAS19010LG2	6U	10.50
PBAS19012BK2	PBAS19012LG2	7U	12.25
PBAS19014BK2	PBAS19014LG2	8U	14.00

Data subject to change without notice

