

# HDA36060

## PowerPact H I-Line Circuit Breaker, ThermMagn, 60A, 3P, 600V, 14kA

Product availability : Stock - Normally stocked in distribution facility



### Main

Product or component type	Circuit breaker
Range of product	PowerPact H
Trip unit technology	Thermal-magnetic
Breaking capacity code	D

### Complementary

Line Rated Current	60 A
Poles description	3P
Breaking capacity	18 kA at 480 V AC 25 kA at 240 V AC 14 kA at 600 V AC 20 kA at 250 V DC
System Voltage	250 V DC 600 V AC
[Ics] rated service short-circuit breaking capacity	80 %
Mounting mode	I-Line
Electrical connection	I-Line connection line Lugs load
AWG gauge	AWG 14...AWG 3/0 (aluminium/copper)
Phase connection	ABC
Magnetic hold current	800 A
Magnetic tripping current	1450 A

### Environment

Product certifications	CSA CE IEC
------------------------	------------------

UL listed

Ambient air temperature for operation 104 °F (40 °C)

## Ordering and shipping details

Category	01112 - HD, JD I-LINE BREAKER/SWITCH
Discount Schedule	DE2
GTIN	00785901419969
Nbr. of units in pkg.	1
Package weight(Lbs)	5.46
Returnability	Y
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0832 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------