

Electronic housing - UCS 237-195-F-GD 9005 - 2203343


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Complete housing for PCBs, can be positioned flexibly; includes housing half shells, side panels closed, adhesive domes for PCB attachment, screws for housing and PCB attachment; light gray housing with turquoise-green corner inlays



Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 404530
GTIN	4055626404530
Weight per Piece (excluding packing)	446.560 g
Custom tariff number	85389099
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

General

Housing material	PC
Color (RAL)	black (9005)

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 100 °C (depending on power dissipation)

Dimensions

Width	237 mm
Height	195 mm
Depth	47 mm

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Electronic housing - UCS 237-195-F-GD 9005 - 2203343

Classifications

eCl@ss

eCl@ss 5.1	27180506
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 5.0	EC001031
ETIM 6.0	EC001031

Accessories

Accessories

Screwdriver tools

Screwdriver - SF-TXH 10X80 - 1200149



Screwdriver, Torx[®] with bore hole, TX 10 x 80, two-component handle