

148-90040

Article Number: 148-90040



Description: HelaCon Plus Mini, Push-In Style Wire Connector, Double Spring, 6-Port, (PC), Violet, 50/pkg

Base Data	Local Order Number	HCPM-6	
	Type	HCPM-6	
	Color	Violet (VT) Clear (CL)	
	Features and benefits	<ul style="list-style-type: none"> • Double-spring technology for safe, secure and reliable connections. • Smaller footprint fits in tight spaces. • Low insertion force makes installation of solid or stranded copper wire fast and easy. • Color coded for easy identification of size. • Each port accepts multiple wire diameters for flexible applications. • Accepts 12–22 AWG solid wire and 14–22 AWG stranded wire. 	
	Quantity Per	box	
	Brand Family	HelaCon	
	Product Description	HelaCon Plus Mini Wire Connectors replace traditional twist-on wire connectors. They provide faster, easier and more reliable connection and distribution of cable and conductors in electrical installation applications. Mini connectors have a compact footprint and can be applied tool-free using convenient, push-in simplicity. Internal double-spring technology is approved for solid and stranded wires.	
	GLOBAL PART NAME (auto set)	HCPM-6-PC-CL/VT	
	Voltage Rating (cULus)	600 V	
	Voltage Rating (VDE)	450 V	
	Short Description	HelaCon Plus Mini, Push-In Style Wire Connector, Double Spring, 6-Port, (PC), Violet, 50/pkg	
	Product Dimensions	Length L (Imperial)	0.65"
		Length L (Metric)	16.5mm
Max Current		24A	
Max Voltage		600V	
Number of Conductors		6	
Width W (Imperial)		1.10"	
Width W (Metric)		28.0mm	

148-90040



Product Dimensions	Height H (Imperial)	0.30"
	Height H (Metric)	7.70mm
	Depth D (imperial)	0.65"
	Depth D (metric)	16.5mm
Material and Specifications		
	Material	Polycarbonate (PC)
	Material Shortcut	PC
	Flammability	UL 94 V0
	Halogenfree	Yes
	Operating Temperature	-22°F to +185°F (-30°C to +85°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
	UL Listed (US and Canada)	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	50
	Package Quantity (Metric)	50Pieces