

LOCTITE[®]

Hey,
*still getting leaks
after so much work?*

**Yeah,
no wonder!**
*My plumber's still
not using LOCTITE 55*



LOCTITE 55

The fast, easy and secure
threaded pipe-sealing cord

Now 160 m.

Test it.

Benefit.



Henkel

Excellence is our Passion

A better joint for pipe systems

Modern technology, traditional skills

LOCTITE 55 pipe-sealing cord is the fast, easy and secure sealant for threaded pipes.

Fast application and an instant seal – it could not be easier. It saves you up to 50% of the time you need with traditional tapes or hemp and paste combinations.

Work fast and clean and save yourself time and money.

A single reel of LOCTITE 55 will seal:

Thread size	1/2	3/4	1
Approx. number of joints – 160 metre pack	405	275	190
Approx. number of joints – 50 metre pack	125	85	60



Benefits in using LOCTITE 55:



Fast, clean and easy to use



Re-adjustment up to 45°



For metal & plastic joints



WRAS:
Approval for use with
potable water up to
85°C (BS 6920)



BAM:
Certificate for ignition
sensitivity to gaseous oxygen
Max. temp.: up to 60°C
Max. oxygen pressure:
up to 20 bar



DVGW:
Approval for gas and water
(EN 751-2, Class ARp)

KTW:
Approval for potable water



NSF:
Certified to NSF / ANSI,
Standard 61

How to apply



For chrome & stainless steel fittings slightly roughen the thread.



Wind the sealing cord onto the first pitches clockwise and cross over the threads. See the pack for the correct number of turns.



Cut the cord using the attached cutting device and press the loose end onto the thread.



Screw the fittings with a pipe wrench. Only reposition if necessary.

Newly designed dispenser

NEW

→ Mess-free

→ Ergonomic design



→ Hassle-free cutting with integral blade

→ One component & one product does all – gas, water, etc

→ Now with more content: **160 m**



LOCTITE®
BONDERITE®
TECHNOMELT®
TEROSON®
AQUENCE®

Henkel Ltd.

Wood Lane End,
Hemel Hempstead, Herts
HP2 4RQ
Tel: 01442 278000
www.loctite55.co.uk

www.loctite55.co.uk

The data contained herein are intended as reference only. Please contact Henkel AG & Co. KGaA for assistance and recommendation on specifications for these products.

® designates a trademark of Henkel AG & Co. KGaA or its affiliates, registered in Germany and elsewhere

© Henkel AG & Co. KGaA, 2016