

1567 TORX® BO Screwdriver for tamper-proof TORX® screws,  
TX 15 x 80 mm  
Resis-TORX driver



EAN	4013288039231	Dimension:	178x33x33 mm
Code:	05030127001	Weight:	56 g
Article-No.		Country of origin:	CZ
		Customs tariff no.:	82054000

- For TORX® socket screws with safety pin
- ESD-safe tool thanks to surface resistance of  $< 10^9$  Ohm
- Multi-component Kraftform Micro handle with anti-roll feature and swivel cap
- For TORX® socket screws with safety pin
- The Wera Black Point tip offers an exact fit and optimum corrosion protection

ESD-safe Micro screwdriver. Dependable protection against electrostatic energy and associated damage. TORX® BO screws have a protruding pin in their drive profile. This effectively prevents any unauthorised loosening since such screws cannot be actuated with normal TORX® tools. Only special TORX® BO tools have a corresponding bore hole for the take-up of the pin. Rapid twisting results from fixing the hand on the swivel cap and by rotating the fast-turning zone just below. This makes time-consuming grip adjustments unnecessary. Power zones with integrated soft sections ensure the transfer of high loosening and tightening torque a precision zone provides for the right rotation angle during fine adjustment work. The Black Point tip offers optimised corrosion protection and an exact fit.