

# EAO – Your Expert Partner for Human Machine Interfaces

61-6461.4047 - Emergency-stop switch compact, foolproof EN IEC 60947-5-5

## 61-6461.4047 - Emergency-stop switch compact, foolproof EN IEC 60947-5-5



*Attention: The preview is based on a sample product. This can differ from your current configuration.*

### Mounting

Mounting cut-out  
Design Ø 16 mm  
raised

### Front

Front shape round  
Front dimension Ø 40 mm

### Other Attributes

Marking Arrows  
Weight 0.018 kg

### Operating-/Indication part

Lens material Plastic  
Lens colour red  
Lens profile Mushroom

### IP-Rating

Front protection IP67, IP69K

### Connection Method

Terminal Solder 2.8 x 0.5 mm

### Actuator

Switching action Maintained

### Switching element

Contacts 1 NC


### Function

Emergency stop switch

# EAO – Your Expert Partner for Human Machine Interfaces


61-6461.4047 - Emergency-stop switch compact, foolproof EN IEC 60947-5-5

## Dimensions




L1 = Solder/Plug-in terminal 2.8 x 0.5 mm


## Mounting cut-outs



## Wiring diagram



## Component layout



## Additional information

Twist to unlock clockwise  
Position indication ring green  
Application as per DIN EN ISO 13850 and EN 60204-1

## Legend

Switching action: C = Maintained