

# OC10G03PNBN00NB3



Products → Low Voltage Products and Systems → Switches → Cam Switches

## General Information

<b>Extended Product Type:</b>	OC10G03PNBN00NB3
<b>Product ID:</b>	1SCA134996R1001
<b>EAN:</b>	6417019637341
<b>Catalog Description:</b>	OC10G03PNBN00NB3 Cam switch
<b>Long Description:</b>	OC10 Cam switch, I <sub>th</sub> =10A, ON-OFF, 3-contacts, Snap-on door mounting, Black Basic handle. Black handle and frontplate with standard text are included. Special engraved frontplates to be ordered as separate items.

## Additional Information

<b>Ampere Rating UL/CSA:</b>	600 V AC 10 A
<b>Color:</b>	Black
<b>Conventional Free-air Thermal Current (I<sub>th</sub>):</b>	q = 40 °C 10 A
<b>Conventional Thermal Current (I<sub>the</sub>):</b>	Fully Enclosed 10 A
<b>Country of Origin:</b>	Finland (FI)
<b>Customs Tariff Number:</b>	85365080
<b>Data Sheet, Technical Information:</b>	1SCC302009C0201
<b>Declaration of Conformity - CE:</b>	1SCC302005D0201
<b>EAN:</b>	6417019637341
<b>ETIM 5:</b>	EC002611 - Control switch
<b>ETIM 6:</b>	EC002611 - Control switch
<b>Enclosure Type:</b>	Not enclosed
<b>Function:</b>	B3
<b>Handle Type:</b>	Basic handle
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Industrial IT Certification Level:</b>	0
<b>Instructions and Manuals:</b>	1SCC302013F0006
<b>Invoice Description:</b>	OC10G03PNBN00NB3 Cam switch
<b>Minimum Order Quantity:</b>	1 piece
<b>Mounting Type:</b>	Snap-on door mounting
<b>Number of Contacts:</b>	3
<b>Number of Poles:</b>	3
<b>Object Classification Code:</b>	Q
<b>Order Multiple:</b>	1 piece
<b>Package Level 1 EAN:</b>	6417019637341
<b>Package Level 1 Gross Weight:</b>	0.05 kg
<b>Package Level 1 Height:</b>	50 mm
<b>Package Level 1 Length:</b>	108 mm
<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	50 mm
<b>Pollution Degree:</b>	3
<b>Power Loss:</b>	0.6 W
<b>Price Category:</b>	Standard
<b>Product Main Type:</b>	OC10
<b>Product Name:</b>	Cam switch
<b>Product Net Depth:</b>	81 mm

Product Net Depth:	32 mm
Product Net Height:	32 mm
Product Net Weight:	0.05 kg
Product Net Width:	32 mm
Rated Continuous Thermal Current:	10 A
Rated Impulse Withstand Voltage ( $U_{imp}$ ):	2.5 kV
Rated Insulation Voltage ( $U_i$ ):	500 V
Rated Operational Current AC-22A ( $I_e$ ):	(500 V) 10 A
Rated Operational Current AC-23A ( $I_e$ ):	(230 V) Three Phase 7.6 A (400 V) Three Phase 6.5 A
Rated Operational Power AC-23A ( $P_e$ ):	(230 V) Three Phase 1.8 kW (400 V) Three Phase 3 kW
Rated Operational Voltage:	500 V
Rated Short-time Withstand Current ( $I_{cw}$ ):	for 1 s 0.12 kiloampere rms
Selling Unit of Measure:	piece
Short Description:	OC10 Cam switch, Ith=10A, ON-OFF, 3-contacts, Snap-on door mounting, Black Basic handle
Special Functions:	ON - OFF switch: 0-position: 9 o'clock, step angle 90°, front plate 0 OFF-1 ON
Terminal Type:	Screw Terminals
Wiring Diagram:	1SCC302014M0201

