

# ONU1KB



Products → Low Voltage Products and Systems → Switches → Cam Switches

## General Information

|                               |  |
|-------------------------------|--|
| <b>Extended Product Type:</b> | ONU1KB   |
| <b>Product ID:</b>            | 1SCA022532R7740  |
| <b>EAN:</b>                   | 4034656520779  |
| <b>Catalog Description:</b>   | ONU1KB Cam switch  |
| <b>Long Description:</b>      | Black handle and frontplate with standard text are included. Special engraved frontplates to be ordered as separate items. |

## Additional Information

|  |  |
|--|--|
| <b>ABB Industrial IT Suite:</b>                                | Control IT   |
| <b>Ampere Rating UL/CSA:</b>                                   | 600 V AC 25 A  |
| <b>Color:</b>  | Black  |
| <b>Conventional Free-air Thermal Current (I<sub>th</sub>):</b> | q = 40 °C 25 A   |
| <b>Country of Origin:</b>                                      | Germany (DE)   |
| <b>Customs Tariff Number:</b>                                  | 85365080   |
| <b>Data Sheet, Technical Information:</b>                      | 1SCC302003C0201  |
| <b>Declaration of Conformity - CE:</b>                         | 1SCC302001D0204  |
| <b>EAN:</b>  | 4034656520779  |
| <b>ETIM 5:</b>   | EC002611 - Control switch  |
| <b>ETIM 6:</b>   | EC002611 - Control switch  |
| <b>Enclosure Type:</b>   | Not enclosed   |
| <b>Environmental Information:</b>                              | 1SCC302003D0201  |
| <b>Function:</b>   | U1   |
| <b>Handle Type:</b>  | Key operated   |
| <b>IT Publishing Status:</b>                                   | Level 0 - Information enabled  |
| <b>Industrial IT Certification Level:</b>                      | 0  |
| <b>Instructions and Manuals:</b>                               | 1SCC302004M0203  |
| <b>Invoice Description:</b>                                    | ONU1KB Cam switch  |
| <b>Minimum Order Quantity:</b>                                 | 1 piece  |
| <b>Mounting Type:</b>  | Snap-on door mounting  |
| <b>Number of Contacts:</b>                                     | 2  |
| <b>Number of Poles:</b>  | 1  |
| <b>Object Classification Code:</b>                             | Q  |
| <b>Package Level 1 EAN:</b>                                    | 4034656520779  |
| <b>Package Level 1 Gross Weight:</b>                           | 0.12 kg  |
| <b>Package Level 1 Height:</b>                                 | 48 mm  |
| <b>Package Level 1 Length:</b>                                 | 93 mm  |
| <b>Package Level 1 Units:</b>                                  | 10 piece   |
| <b>Package Level 1 Width:</b>                                  | 48 mm  |
| <b>Price Category:</b>   | Standard   |
| <b>Product Main Type:</b>                                      | ON   |
| <b>Product Name:</b>   | Cam switch   |
| <b>Product Net Depth:</b>                                      | 93 mm  |
| <b>Product Net Height:</b>                                     | 48 mm  |
| <b>Product Net Weight:</b>                                     | 0.12 kg  |
| <b>Product Net Width:</b>                                      | 48 mm  |
| <b>Rated Continuous Thermal Current:</b>                       | FullyEnclosed 25 A   |
| <b>Rated Operational Voltage:</b>                              | 400 V  |
| <b>Replacement Product ID (NEW):</b>                           | 1SCA126492R1001  |
| <b>RoHS Information:</b>                                       | 1SCC302004D0201  |
| <b>Selling Unit of Measure:</b>                                | piece  |
| <b>Short Description:</b>                                      | Cam switch. Change-over switches. Normal, door mounted                             |
| <b>Special Functions:</b>                                      | Change-over switch: With 0-position: 12 o'clock, step angle 60°, front plate 1-0-2 |
| <b>Terminal Type:</b>  | Screw Terminals  |

