



Share:



SRT192BP

★★★★★
Be the first to [write a review](#)
Share this Product:



Includes : Documentation CD , Installation guide , Warranty card



Product Overview **Technical Specifications** Documentation Drawings Options Ratings & Reviews

Batteries & Runtime

Print Technical Specification

Battery type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Battery mounting	Stand alone battery stack
Expected Battery Life (years)	3 - 5
RBC Quantity	2

Physical

Maximum Height	17.0inches (432mm , 43.2CM)
Maximum Width	5.1inches (130mm , 13.0CM)
Maximum Depth	26.88inches (682mm , 68.27CM)
Net Weight	200.2lbs. (91.0KG)
Shipping weight	223.3lbs. (101.5KG)
Shipping Height	16.54inches (420mm , 42.0CM)
Shipping Width	23.63inches (600mm , 60.0CM)
Shipping Depth	39.38inches (1000mm , 100.0CM)
Color	Black
Units per Pallet	1.0

Environmental

Operating Temperature	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95% no %
Operating Elevation	0-10000ft (0-3000meters)
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95% no %
Storage Elevation	0-15000ft (0-4500meters)

Conformance

Standard warranty	2 years repair or replace
-------------------	---------------------------

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs



Sign up to stay up to date with best practices, new solutions and special offers.

Email

I am a...



OK

[Contact Us](#)
[Rate this website](#)

[TERMS & CONDITIONS](#) | [PRIVACY STATEMENT](#)

© 2018, APC by Schneider Electric

