

UL LISTED CE SF Pan-Ty® Cable Ties – Nylon 6.6

- Versatile cable ties can be used in countless applications
- One-piece construction for consistent performance and reliability
- Lowest threading force of any one-piece cable tie in the industry

- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation
- A variety of materials and colors available for specific applications
- UL Listed for use in plenum or air handling spaces per NEC except PLT.6SM and PLT5H/6H/8H/13H, PLT5EH/6EH



EH Series

Part Number	Length		Width		Thickness		Max. Bundle Dia.		Min. Loop Tensile Str.		Recommended Installation Tool	Std. Pkg. Qty.	Std. Ctn. Qty.
	In.	mm	In.	mm	In.	mm	In.	mm	Lbs.	N			
Miniature Cross Section – Plenum-Rated													
PLT1M-C	3.9	99	0.098	2.5	0.043	1.1	0.87	22	18	80	GTS, GTSL, GS2B, PTS, PPTS, STS2	100	1000
PLT1.5M-C	5.6	142	.098	2.5	0.043	1.1	2.5	32	18	80		100	1000
PLT2M-C	8.0	203	.098	2.03	0.043	1.1	2.00	51	18	80		100	1000
Intermediate Cross Section – Plenum-Rated													
PLT1.5I-C	5.6	142	.142	3.6	0.045	1.1	1.38	35	40	178	GTS, GTSL, GS2B, PTS, PPTS, STS2	100	1000
PLT2I-C	8.0	203	.142	3.6	0.045	1.1	2.00	51	40	178		100	1000
PLT2.5I-C	9.7	246	.145	3.7	0.052	1.3	2.50	64	40	178		100	1000
PLT3I-C	11.4	290	.145	3.7	0.052	1.3	3.00	76	40	178		100	1000
PLT4I-C	14.5	368	.145	3.7	0.052	1.3	4.00	102	40	178		100	1000
Standard Cross Section – Plenum-Rated													
PLT1S-C	4.8	122	.190	4.8	0.052	1.3	1.00	25	50	222	GTS, GTSL, GS2B, GTH, GS4H, PTS, PPTS, PTH, STS2, STH2	100	1000
PLT1.5S-C	6.2	157	.190	4.8	0.052	1.3	1.50	38	50	222		100	1000
PLT2S-C	7.4	188	.190	4.8	0.052	1.3	1.88	48	50	222		100	1000
PLT2.5S-C	9.8	249	.190	4.8	0.052	1.3	2.50	64	50	222		100	1000
PLT3S-C	11.5	292	.190	4.8	0.052	1.3	3.00	76	50	222		100	1000
PLT4S-C	14.5	368	.190	4.8	0.052	1.3	4.00	102	50	222		100	1000
PLT4.5S-C	15.5	394	.190	4.8	0.052	1.3	4.50	114	50	222		100	1000
PLT5S-C	17.5	445	.190	4.8	0.052	1.3	5.00	127	50	222		100	500
Light-Heavy Cross Section (Straight Tip) – Plenum-Rated													
PLT2H-L	8.1	206	.300	7.6	0.075	1.9	2.00	51	120	534	GTH, GS4H, GS4EH, PTH, STH2, ST3EH	50	500
PLT2.5H-L	9.8	251	.300	7.6	0.075	1.9	2.50	64	120	534		50	500
PLT3H-L	11.4	290	.300	7.6	0.075	1.9	3.00	76	120	534		50	500
PLT4H-L	14.5	368	.300	7.6	0.075	1.9	4.00	102	120	534		50	500
PLT6LH-L	21.9	556	.300	7.6	0.075	1.9	6.00	152	120	534		50	500
PLT7LH-L	24.7	627	.300	7.6	0.075	1.9	7.00	178	120	534		50	500
PLT8LH-L	27.6	701	.300	7.6	0.075	1.9	8.00	203	120	534		50	500
PLT9LH-L*	30.5	775	.300	7.6	0.075	1.9	9.00	229	120	534		50	500
PLT10LH-L*	34.3	871	.300	7.6	0.075	1.9	10.31	262	120	534		50	1000
Heavy Cross Section (Straight Tip)													
PLT5H-L*	17.7	450	.350	4.50	0.078	2.0	5.00	127	175	778	GTH, GS4H, GS4EH, PTH, STH2, ST3EH	50	500
PLT6H-L*	20.9	530	.350	8.9	0.078	2.0	6.00	152	175	778		50	500
PLT8H-L*	30.6	779	.350	8.9	0.078	2.0	9.00	229	175	778		50	500
PLT13H-Q*	43.3	1100	.350	8.9	0.078	2.0	13.00	330	175	778		25	500
Extra-Heavy Cross Section (Straight Tip)													
PLT5EH-Q	20.1	511	0.500	12.7	0.075	1.9	5.00	127	250	1112	GS4EH, ST3EH	25	250
PLT6EH-Q	22.2	564	0.500	12.7	0.075	1.9	6.00	152	250	1112		25	250

*UL Listed – meets the requirements of UL 181B-C, for use with UL non-metallic air ducts and air connectors. UL Recognized except PLT5EH/6EH.