



Sample photo

Order symbol: PCQ3 122410
Product nbr: 7035781
Description: Enclosure, PC
Remarks: Grey cover (quick-locking)

EAN: 6418074099075
EI. number:
Finland: 3424188

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and quick-locking cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	244	124	97	TRM 0812	DIN-15 Mounting rail
inch:	9.6	4.9	3.8	MIN 20	DIN-15 Mounting rail
Materials:				TRH 1212	DIN-35 Mounting rail
Material:	Polycarbonate			TRH 24	DIN-35 Mounting rail
Base colour:	RAL 7035 -light grey			TF 28037	Wall fastening lug (4 pcs)
Cover screws material:	Stainless steel			TH A	Grey plastic hinges (2 pcs)
Cover colour:	RAL 7035 -light grey			EU 3 QuickLock set 60	QuickLock screws (60 pcs)
Gasket material:	Polyurethane			MR 28036EU Set 60	Mounting screws (60 pcs)
Temperatures:				EU 3 Plug set 60/30	EU 3 Cover screw plug set 60/30
Temperature °C (short term):	-40 ... 120 °C			EU 3 Plug set 60/30 BL	EU 3 Cover screw plug set 60/30 black
Temperature °C (continuous):	-40 ... 80 °C			Rating:	
Temperature °F (short term):	-40 ... 250 °F			Ingress Protection (EN 60529): IP66/IP67	
Temperature °F (continuous):	-40 ... 175 °F			Impact Resistance (EN 62262): IK07	
Accessories:				Electrical insulation: Totally insulated	
TM 1224	Mounting plate			Halogen free (DIN/VDE 0472, Part 815): 1	
Certificates:				Glow Wire Test (IEC 695-2-1) °C: 650	
				SGS Fimko	
				Gost R	

