


KEMET, L-DWI, Power, 1500 nH, 20%



Dimensions	
Chip Size	1210
L	3.2mm +/-0.2mm
W	2.5mm +/-0.2mm
T	2.5mm +/-0.2mm
LL	0.6mm +/-0.3mm

Packaging Specifications	
Packaging:	T&R
Packaging Quantity:	1000

General Information	
Series:	L-DWI
Style:	SMD Chip
Description:	Surface Mount Inductor
Features:	High Current Type
RoHS:	Yes

Specifications	
Inductance:	1.5 uH (0.1 MHz)
Inductance Tolerance:	20%
Temperature Range:	-40/+105C
Current:	2000 mAmps (Isat, 30% Drop In Inductance), 1310 mAmps (Irms, 40C Rise By Self Heating)
Self-Resonant Frequency:	220 MHz