



Search



Rollover image to zoom



DCF680N2

8V MAX* GYROSCOPIC SCREWDRIVER 2 BATTERY KIT

★★★★☆ 3.0 (2) [WRITE A REVIEW](#)

The DCF680N2 8V MAX* Gyroscopic Screwdriver 2 Battery Kit is ideal for achieving precision, speed, and control. Adjustable two-position handle allows for operation in either in-line or pistol-grip to suit the professional's needs.

BUY NOW

SHARE THIS PRODUCT:

IMPORTANT LINKS

[FEATURES & SPECS](#)

[WARRANTY](#)

[FAQS](#)

[USER REVIEWS](#)

FEATURES & SPECS

FEATURES

- Motion activation variable speed and reversing control for precise fastening control
- Motion activated variable speed 0-430 rpm for fastening into wood, plastic, and light-gauge metal
- Adjustable two-position handle allows for operation in either in-line or pistol-grip
- Allows control when completing light fastening applications
- LED provides illumination in confined areas without shadowing
- Battery charge status on tool notifies when to charge packs
- 1/4" hex allows for quick screwdriver bit change and holds 1" bit tips
- 8V MAX battery pack allows for longer run-time and charges in one hour

SPECIFICATIONS

DRIVE	1/4" HEX
NO LOAD SPEED	0-430 RPM
POWER TOOL TYPE	CORDLESS
SYSTEM	8V MAX*
TOOL WEIGHT	1.1 LBS

INCLUDES

- 1 hour charger
- (2) 8V MAX compact batteries
- Kit Bag

WARRANTY & SERVICE INFORMATION

WARRANTY INFORMATION



MANUALS

[INSTRUCTION MANUAL](#) ▶▶

LOOKING FOR SERVICE?

FAQS



2014 FERGUSON DW/PROTO JUNE REBATES 6-1-14
EXPAND TO SEE ANSWER



WHAT IS THE TORQUE RATING OF THE DCF680?
EXPAND TO SEE ANSWER

★★★★★ 3.0 | 2 Reviews

1 out of 1 (100%) reviewers recommend this product

Search topics and reviews



Reviews

[WRITE A REVIEW](#)

Rating Snapshot

Average Customer Ratings