

**PRODUCTS**

**RESOURCES**

**SUPPORT**

**COMPANY**

**CONNECT**

Home » Catalog » Fish Tapes & Conduit Tools » Fish Tapes » Fiberglass Fish Tapes

# 100' Fiberglass Fish Tape



## Cat. No. 56010

### Product Features

*Permanent, laser etched 1' increments on the tape allow you to more accurately measure the depth of conduit runs and determine the amount of tape left to pay out*

*Non-conductive, fiberglass fish tape slides easily over existing wires and through multiple bends*

*The lightweight, strong fiberglass tape resists harsh elements and is strength rated up to 500 pulling pounds*

*The 13" case diameter means you can reel in 15% more tape in a single revolution vs. a standard 12" case*

*Durable 7" leader helps push through crowded conduit*

*Raised fingergrrips help transfer 100% of the winding power from your hand and fingers*

*Unique sloped handle optimizes the position of your hand for quick hand-over-hand rewinds and allows a more level payout of tape on the backswing while feeding conduit*

*Repair kit (Cat. No. 56115), replacement eyelets (Cat. No. 56116) and spiral leaders (Cat. No. 56120) available*



**BUY NOW**

**FIND RETAILER**



**Specs**

**Video**

**Downloads**

**Warnings**

**Accessories**

**Replacement Parts**

**Tape Size:** 100' x 3/16" (30.5 m x 4.8 mm)

**Weight:** 3.5 lb (1.6 kg)

**Diameter:** 13" (330.2 mm)

**UPC:** 092644560101

[partner support](#) | [american manufacturing](#) | [klein tradesman club](#) | [warranty](#) | [contact us](#) | [klein gear](#)