

## 25' Double Hook Magnetic Tape Measure



**Cat. No. 86225**

### Product Features

- Uncluttered, easy-to-read bold lines marked on blade every 1/8 inch*
- Dual angle magnetic hooks attach to conduit and steel studs*
- Heavy-duty nylon-coating protects blade printing*
- Retraction speed brake controls blade speed and protects fingers from touching blade*
- Blade printed Conduit Bending Table helps calculate offsets and saddles*
- Super-sized back clip holds securely to wide belts and extends deep into pockets*
- Up to 9-1/2 ft. stand-out*
- U.S. Patent Pending*

**BUY NOW**

**FIND RETAILER**



**Specs**

**Video**

**Downloads**

**Warnings**

**Accessories**

**Related Items**

**Type:** Double Sided  
**Tape Length:** 25 ft (7.6 m)  
**Tape Coating:** Nylon  
**Graduations:** 1/16"  
**Rewind Type:** Automatic  
**Magnetic:** Yes  
**Case Material:** ABS Plastic  
**Overall Width:** 4-1/4" (108.0 mm)  
**Overall Length:** 6-1/2" (165.1 mm)  
**UPC:** 092644862250

**Special Features:** Uncluttered, Easy to Read Bold Lines Every 1/8"

**Tape Material:** Steel  
**Measurement Standard:** SAE  
**Lockable Tape:** Yes  
**Hook:** Double  
**Belt Clip:** Yes  
**Case Color:** Orange  
**Overall Height:** 2-1/4" (57.2 mm)  
**Weight:** 1.1 lb (0.5 kg)