



PRODUCTS

RESOURCES

SUPPORT

COMPANY

CONNECT

Home » Catalog » Pliers » Diagonal-Cutting Pliers » High-Leverage Diagonal-Cutting Pliers

Journeyman™ Diagonal-Cutting Pliers



Cat. No. J228-8

Product Features

- High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting power than other plier designs
- Short jaws and beveled cutting edges permit close cutting of wire
- Induction-hardened cutting knives for long life
- Hot-riveted joint ensures smooth action and no handle wobble
- State-of-the-art, dual-material Journeyman™ handles provide a better grip without sacrificing tool strength and durability
- Hard, black material for toughness and durability
- Soft material on outer surface for comfort and a firm grip
- Color-coded handles allow quick identification of tool
- Custom, US-made tool steel



BUY NOW

FIND RETAILER



Specs Downloads Warnings Accessories

Type: Journeyman Diagonal Cutting Pliers
Material: Steel
Jaw Width: 1-3/16" (30.2 mm)
Jaw Capacity: 1" (25.4 mm)
Cut Style: Standard
Handle Color: Red/Black
Handle Length: 6-1/2" (165.1 mm)
Tether Capable: No
UPC: 092644721076

Overall Length: 8-1/8" (206.4 mm)
Jaw Length: 13/16" (20.6 mm)
Jaw Thickness: 13/16" (20.6 mm)
Cutting Knives: Standard
Joint Type: Adjustable
Handle Finish: Journeyman
Insulated: No
Weight: 0.67 lb (0.30 kg)

[partner support](#) | [american manufacturing](#) | [klein tradesman club](#) | [warranty](#) | [contact us](#) | [klein gear](#)