

# RF / Coaxial Cable Assembly

## Rear Lock IP67 SMA Bulkhead Jack-to-MMCX Right Angle Plug, 200mm




**RoHS  
Compliant**



### Electrical Performance:

|                                 |                |
|---------------------------------|----------------|
| Impedance                       | : 50Ω          |
| Frequency Range                 | : DC ~ 6.0 Ghz |
| Working Voltage                 | : 170Vrms Max. |
| Dielectric Withstanding Voltage | : 500Vrms Max. |
| Insulator Resistance            | : 1000MΩ Min.  |




Dimensions : Millimetres


| Sl. | Description  | Qty |
|-----|--|-----|
| 1   | SMA Rear Lock B/H Jack Crimp for OD 1.37mm Cable conn. | 1   |
| 2   | MMCX Right Angle Plug for OD 1.37mm Cable              |     |
| 3   | 1.37mm Black Cable                                     | 2   |
| 4   | Heat Shrink Tube F32 Ø2.5mm L=15mm Colour: Black       |     |

| Specification  | DC ~ 6.0 GHz  |
|----------------|---------------|
| VSWR           | 1.65 : 1 Max. |
| Insertion Loss | -1.1 dB Max.  |


1 PCS/1PE BAG SIZE:4.5"x3.5"



⑥ 3.5"x4.5" PE BAG LABEL SIZE:60x40mm





⑧ 11"x13" PE BAG LABEL SIZE:40x15mm



# RF / Coaxial Cable Assembly

Rear Lock IP67 SMA Bulkhead Jack-to-MMCX Right Angle Plug, 200mm



**Note:**

- 1. 1 piece finished Product (include nut and washer)/1 PE Bag
- 2. 11" x 13" PE bag (600 pcs)/1 Carton

| Item | Description                                 | Qty |
|------|---|-----|
| 5    | PE Bag 0.07mm, 3.5" x 4.5"                  | 1   |
| 6    | 3.5" x 4.5" PE Bag Lable size : 60mm x 40mm |     |
| 7    | PE Bag 0.07mm, 11" x 13"                    |     |
| 8    | 11" x 13" PE Bag Lable Size: 40mm x 15mm    |     |
| 9    | Carton, Size: 33cm x 22cm x 22cm            |     |
| 10   | RoHS Logo Lable size: 45mm x 20mm           |     |

**Part Number Table**

| Description  | Part Number |
|--|-------------|
| RF / Coaxial Cable Assembly<br>Rear Lock IP67 SMA Bulkhead Jack-to-MMCX<br>Right Angle Plug, 200mm | MC001914    |

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com  
www.farnell.com  
www.newark.com

