

74 05 250

High Leverage Diagonal Cutter



- For very tough, continuous use
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Precision cutting edges additionally induction hardened (cutting edge hardness approx. 64 HRC), for all sorts of wire including piano wire
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened
- The 250-mm-long diagonal cutter is suitable for copper conductors up to 16 mm² and aluminium conductors up to 35 mm²




20 % less effort required

compared to conventional diagonal cutters of the same length.

With integrated forged joint axle.

Article No.	74 05 250
EAN	4003773039754
Pliers	chrome plated
Handles	with multi-component grips
Style	0
Head	
Cutting capacities medium hard wire (diameter) Ø mm	4,6
Cutting capacities hard wire (diameter) Ø mm	3,5
Cutting capacities piano wire (diameter) Ø mm	3,0
Length mm	250
Net weight g	440



technical change and errors excepted

