

95 61 150

Bowden Cable Cutter



- For Bowden cables and soft wire rope up to 3.0 mm dia. (also V2A)
- Smooth and clean cutting due to special shape of the cutting edges
- Sickle shape cutting edges surround the material and prevent the wire rope fanning out
- Little handforce required due to very high transmission ratio
- With opening spring and locking device
- Cutting edges additionally induction hardened
- High-grade special tool steel, forged, multi stage oil-hardened



Article No.	95 61 150
EAN	4003773065197
Shears	black atramentized
Head	polished
Handles	plastic coated
Cutting capacity copper cable, fine-stranded (diameter) Ø mm	3
Cutting capacities wire rope (diameter) Ø mm	3
Length mm	150
Net weight g	205



technical change and errors excepted



Spare Parts

Article No.	EAN	
95 69 190 01	4003773053873	Joint screw, nut and washer for 95 61 190