

97 61 145 F

Crimping Pliers for end sleeves (ferrules)



- For crimping end sleeves (ferrules) according to DIN 46228 parts 1 + 4 in the range from 0.25 up to 2.5 mm²
- Crimping in marked trapezoidal dies for reliable connections between the sleeve and the conductor
- Vanadium electric steel; forged, oil-hardened



Article No.	97 61 145 F
EAN	4003773043980
Head	polished
Handles	plastic coated
Applications	End Sleeves (ferrules)
Capacity in square millimetres mm²	0,25 - 2,5
Number of crimping positions	4
AWG	23 - 13
Length mm	145
Net weight g	140

technical change and errors excepted

