

98 20 40

Screwdrivers for slotted screws



- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel



Article No.	98 20 40
EAN	4003773026402
Tip	burnished
Handle	insulating multi-component handle, VDE-tested
Insulation standard	IEC 60900 DIN EN 60900
Blade width mm	4,0
Blade length mm	100
Handle length mm	102
Nominal size	4,0 mm
Length of non-insulated blade mm	15
Blade thickness mm	0,8
Length mm	202
Net weight g	38

technical change and errors excepted

