

ZCY44

limit switch lever ZCY - thermoplastic pliable roller
lever variable length

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCY
Product compatibility	XCKD XCKP XCKT XCMD
Associated head	ZCE01 ZCE05
Movement of operating head	Rotary
Type of operator	Pliable roller lever spring return thermoplastic (variable length)
Tracks	No track
Type of approach	Lateral approach

Complementary

Switch actuation	By 30° cam
Positive opening	With

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22413 - LIMIT SWITCH, IEC, MINIATURE
----------	--------------------------------------

Discount Schedule	T
GTIN	003389110191981
Nbr. of units in pkg.	1
Package weight(Lbs)	5.999999999999998E-2
Returnability	Y
Country of origin	ID

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0851 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------