

Product data sheet

Characteristics

P6M10

APC Essential SurgeArrest, 6 outlets, 10ft cord, metal housing, 120V



Overview

Model Name	APC Essential SurgeArrest, 6 outlets, 10ft cord, metal housing, 120V
Standard Lead Time	Usually in Stock
Product Distribution	Canada , United States

Output

Number of Outlets	6
Receptacle Style	NEMA 5-15R

Input

Nominal Input Voltage	120V
Input Power	1875 W
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	NEMA 5-15P
Maximum Line Current per phase	0.0 A
Cord Length	3.05 meters
Maximum Input Current	15 A

Surge Protection and Filtering

Surge energy rating	540 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	0.0 dB
Peak Current Common Mode	0.0 kA
NM Surge Response Time (ns)	0.0 NS
Let Through Voltage Rating	330

Physical

Net Weight	0.7 kg
Maximum Height	311.0 mm
Maximum Width	63.0 mm
Maximum Depth	38.0 mm
Shipping Weight	0.8 kg
Shipping Height	335.0 mm
Shipping Width	100.0 mm
Shipping Depth	1168.0 mm
Master Carton Units	12.0
Master Carton Dimensions (Length x Width x Height)	15.5 x 9 x 12.75 inches
Master Carton Weight	11.0 kg
SCC Codes	1073130425320 1
Color	Grey
Units per Pallet	288.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-15000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

Conformance

Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$25000
UL 1449 TVSS Rating	330

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs