

MA0510BIM-3PIN –

Case Fan, 3 Pin, 50 mm x 50 mm x 10 mm



FAN, 50MM, 3 PIN
Fan Size : 50mm x 50mm
Current Type : DC
External Diameter : 50mm
External Height : 50mm
External Width : 50mm
Flow Rate - Imperial : 9.59cu.ft/min
Flow Rate - Metric : 0.27m³/min
Noise Figure Typ : 23dB
Power Consumption : 1.08W
Speed Range Max : 4500rpm
Supply Voltage : 12V
Supply Voltage V DC : 12V