



Supplier of Industrial and Consumer Batteries, Chargers, and Battery Packs

JOIN OUR NEWSLETTER

SEARCH

BROWSE BY
**PRODUCT
CATEGORY**

BROWSE BY
**DEVICE
MANUFACTURER**

ADVANCED
**INDUSTRIAL
SEARCH**

[Home](#) / CUSTOM-255 LONG



PART#: CUSTOM-255 LONG

Chemistry: Nickel Metal Hydride (NIMH)
Voltage: 4.8
Capacity: 750mAh
Measurements: 6.9" x 0.4"
 175.26mm x 10.16mm

[Find a Distributor](#)

hover to zoom; click to enlarge

This replacement 4.8 Volt 750 mAh Nickel Metal Hydride battery is used in the Chloride - 1000030142 Emergency Lighting and meets or exceeds original manufacturer specifications.

SPECIFICATIONS

Shipping Weight (oz)	1.8000
Manufacturer	Dantona
Warranty	6
UPC	728286975347
Length	6.9" (175.26mm)
Width	No" (0.00mm)
Height / Diameter	0.4" (10.16mm)
Voltage	4.8
mAh	750
Number of Cells	4
Battery Chemistry	Nickel Metal Hydride (NIMH)
Rechargeable	Rechargeable
Qty Per Package	1
Type of Cell	AAA, Cylindrical
Weight	1.8 oz

Compatible Batteries and Devices

[Batteries \(2\)](#)



IMAGES ARE FOR REFERENCE ONLY! Please note that the capacity (mAh) may change without notice. Always consult the product specifications for correct information. Dantona Industries, Inc. is not affiliated in any way with any of the manufacturers listed in this catalog and the batteries sold in this catalog have not been

CAN'T FIND THE BATTERY YOU NEED?

CALL US AT 1-800-Dantona

TO SPEAK TO A BATTERY EXPERT

VIEW OUR WIDE SELECTION OF

Custom Battery Packs

SHOP OUR CUSTOM PACKS