

Coaxial Cable Connector 25_SMA-50-2-25/111_N

Description

Straight panel cable jack, flange mount

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 18 GHz

Mechanical Data

Centre contact soldered
Outer contact soldered
Weight 0.0019 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU, RoHS compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00009024
Catalogue drawing DCA-00009026
Assembly instruction DOC-0000179086

Ordering Information

Single package 25_SMA-50-2-25/111_NE

Additional Information

Suitable cables EZ_86_TP_M17, SUCOFORM_86, MULTIFLEX_86