

**Order symbol:** AR24208CHSS  
**Product nbr:** 8561155  
**Description:** PC Enclosure  
**Remarks:** Hinged opaque cover w/S.S.  
Quick release latch

**EAN:** 6418074089960  
**El. number:**  
**Finland:**

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:	Length	Width	Height	Rating:
<b>mm:</b>	611	510	205	Ingress Protection (EN 60529): IP66/IP67
<b>inch:</b>	24.1	20.1	8.1	Electrical insulation: Totally insulated
				Halogen free (DIN/VDE 0472, Part 815): 0
				UV resistance: UL 508
				Flammability Rating: UL 508
				Glow Wire Test (IEC 695-2-1) °C: 960
				NEMA Class: UL Type 4X

Materials:	
<b>Material:</b>	Polycarbonate
<b>Base colour:</b>	RAL 7035 -light grey
<b>Cover screws material:</b>	Stainless steel
<b>Cover colour:</b>	RAL 7035 -light grey
<b>Gasket material:</b>	Polyurethane

Temperatures:	
<b>Temperature °C (short term):</b>	-40 ... 140 °C
<b>Temperature °C (continuous):</b>	-40 ... 80 °C
<b>Temperature °F (short term):</b>	-40 ... 284 °F
<b>Temperature °F (continuous):</b>	-40 ... 175 °F

