



Sample photo

Order symbol: AR1084CHSSLT
Product nbr: 8561106
Description: PC Enclosure
Remarks: Hinged transparent cover
w/S.S. Lockable latch

EAN: 6418074066749
EI. number:
Finland:

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:	Length	Width	Height	Accessories:
mm:	254	203	102	ALBP108 Aluminum Back Panel
inch:	10.0	8.0	4.0	ADFP108 Dead Front Panel w/ screws
Materials:				ASP108 Aluminum Swing Panel
Material:	Polycarbonate			ASPK108 Swing Panel Kit incl. Panel
Base colour:	RAL 7035 -light grey			ASPHK10 Swing Panel Kit w/o Panel
Cover screws material:	Stainless steel			AMFL8 8" Mounting Flange Set
Cover colour:	Clear transparent			
Gasket material:	Polyurethane			
Temperatures:				Rating:
Temperature °C (short term):	-40 ... 140 °C			Ingress Protection (EN 60529): IP66/IP67
Temperature °C (continuous):	-40 ... 80 °C			Electrical insulation: Totally insulated
Temperature °F (short term):	-40 ... 284 °F			Halogen free (DIN/VDE 0472, Part 815): 0
Temperature °F (continuous):	-40 ... 175 °F			UV resistance: UL 508
Accessories:				Flammability Rating: UL 508
ABP108	Painted Steel Back Panel			Glow Wire Test (IEC 695-2-1) °C: 960
				NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13

