



Sample photo

Order symbol: AR16148CHLT
Product nbr: 8561075
Description: PC Enclosure
Remarks: Hinged transparent cover w/Plastic quick release latch

EAN: 6418074067241
EI. number:
Finland:

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:	Length	Width	Height	Accessories:
mm:	406	356	203	ALBP1614 Aluminum Back Panel
inch:	16.0	14.0	8.0	ADFP1614 Dead Front Panel w/ screws
Materials:				ASP1614 Aluminum Swing Panel
Material:	Polycarbonate			ASPK1614 Swing Panel Kit incl. Panel
Base colour:	RAL 7035 -light grey			ASPHK16 Swing Panel Kit w/o Panel
Cover screws material:	Stainless steel			AMFL14 14" Mounting Flange Set
Cover colour:	Clear transparent			
Gasket material:	Polyurethane			
Temperatures:				Rating:
Temperature °C (short term):	-40 ... 140 °C			Ingress Protection (EN 60529): IP66/IP67
Temperature °C (continuous):	-40 ... 80 °C			Electrical insulation: Totally insulated
Temperature °F (short term):	-40 ... 284 °F			Halogen free (DIN/VDE 0472, Part 815): 0
Temperature °F (continuous):	-40 ... 175 °F			UV resistance: UL 508
Accessories:				Flammability Rating: UL 508
ABP1614	Painted Steel Back Panel			Glow Wire Test (IEC 695-2-1) °C: 960
				NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13

