



Sample photo

Order symbol: AR20168CHTSS
Product nbr: 8561371
Description: PC Enclosure
Remarks: Hinged opaque cover w/S.S.
 Lockable twist latch

EAN: 6418074089915
El. number:
Finland:

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:	Length	Width	Height	Rating:
mm:	508	406	205	Ingress Protection (EN 60529): IP66/IP67
inch:	20.0	16.0	8.1	Electrical insulation: Totally insulated
Materials:				Halogen free (DIN/VDE 0472, Part 815): 1
Material:	Polycarbonate			UV resistance: UL 508
Base colour:	RAL 7035 -light grey			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws material:	Stainless steel			
Cover colour:	RAL 7035 -light grey			
Gasket material:	Polyurethane			
Temperatures:				
Temperature °C (short term):	-40 ... 140 °C			
Temperature °C (continuous):	-40 ... 80 °C			
Temperature °F (short term):	-40 ... 284 °F			
Temperature °F (continuous):	-40 ... 175 °F			

