

ARCA AR664CHSSL



 Order symbol:
 AR664CHSSL
 EAN:
 6418074066671

Product nbr:8561026El. number:Description:PC EnclosureFinland:

Remarks: Hinged opaque cover w/S.S.

Lockable latch

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Sample photo

Dimensions:	Length	Width	Height	Accessories:	
mm:	152	152	102	ABP66	Painted Steel Back Panel
inch:	6.0	6.0	4.0	ALBP66	Aluminum Back Panel
	0.0	0.0	4.0	ADFP66	Dead Front Panel w/ screws
Materials:				ASP66	Aluminum Swing Panel
Material:	Polycarbor	nate		ASPK66	Swing Panel Kit incl. Panel
Base colour:	RAL 7035 -light grey			ASPHK6	Swing Panel Kit w/o Panel
Cover screws material:	Stainless steel			AMFL6	6" Mounting Flange Set

Rating:

Cover colour: Gasket material: Stainless steel
RAL 7035 -light grey
Polyurethane

Temperatures:

Temperature °C (short term): -40 ... 140 °C
Temperature °C (continuous): -40 ... 80 °C
Temperature °F (short term): -40 ... 284 °F
Temperature °F (continuous): -40 ... 175 °F

Accessories:

APBP66 PVC Back Panel

Ingress Protection (EN 60529): IP66/IP67 Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: UL 508 Flammability Rating: UL 508

Glow Wire Test (IEC 695-2-1) °C: 960 NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13

