



Sample photo

Order symbol: AR16148CHSST
Product nbr: 8561077
Description: PC Enclosure
Remarks: Hinged transparent cover w/S.S. Quick release latch

EAN: 6418074067258
EI. number:
Finland:

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:	Length	Width	Height	Accessories:	
mm:	406	356	203	ALBP1614	Aluminum Back Panel
inch:	16.0	14.0	8.0	ADFP1614	Dead Front Panel w/ screws
Materials:				ASP1614	Aluminum Swing Panel
Material:	Polycarbonate			ASPK1614	Swing Panel Kit incl. Panel
Base colour:	RAL 7035 -light grey			ASPHK16	Swing Panel Kit w/o Panel
Cover screws material:	Stainless steel			AMFL14	14" Mounting Flange Set
Cover colour:	Clear transparent			Rating:	
Gasket material:	Polyurethane			Ingress Protection (EN 60529): IP66/IP67	
Temperatures:				Electrical insulation: Totally insulated	
Temperature °C (short term):	-40 ... 140 °C			Halogen free (DIN/VDE 0472, Part 815): 0	
Temperature °C (continuous):	-40 ... 80 °C			UV resistance: UL 508	
Temperature °F (short term):	-40 ... 284 °F			Flammability Rating: UL 508	
Temperature °F (continuous):	-40 ... 175 °F			Glow Wire Test (IEC 695-2-1) °C: 960	
Accessories:				NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13	
ABP1614	Painted Steel Back Panel				

